

SILQUEST* SILANES

for filler treatment in plastic applications



Product Description


Inorganic fillers are used to reinforce a number of plastic resins. Silanes treated fillers can improve the strength and end use properties of these composites. Often it is advantageous to pre-treat the fillers with silane instead of integrally blending the silane with the filler and plastic resins. These advantages can include more uniform coating of the silane onto the filler and lower use levels when compared to integral blending processes.

Filler particles tend to agglomerate in liquid resins or polymer melts. Poor dispersion creates areas of high and low resin concentrations in the composite part.

Key Features & Typical Benefits

Silane treated filler particles are used to optimize performance by providing:

- Very stable mixture with less agglomeration
- Uniform distribution of filler in resin
- Advanced coupling of filler to polymer matrix



POOR DISPERSION
Untreated filler in polymer

GOOD DISPERSION
Treated filler in polymer

Product Selections

Compatibility of Silquest* silanes varies with the resin being used in composite fabrication. A general guide to silane selection is provided below.

Thermoplastics

POLYMER MATRIX	SILANE TO CONSIDER	SILANE TO CONSIDER FOR LOW VOC
Polyamide (PA6, PA6.6 PA12)	Silquest* A-1108, A-1100 or A-187 silane	Silquest VS-142 or VX-225 silane
Polyester (PET, PBT, PLA)	Silquest A-1100* or A-187 silane	Silquest VS-142 silane
Polypropylene (PP)	Silquest* A-174NT silane	
Polyethylene (PE)	Silquest A-151NT or A-174NT silane	Silquest G-170 silane
Styrenics (ABS, SAN, ASA)	Silquest A-187* silane	
Polyetheretherketone (PEEK)	Silquest A-1100 or A-187 silane	Silquest VS-142 silane
Polyphenylsulfone (PPS)	Silquest A-1100 silane	Silquest VS-142 silane
Polycarbonate (PC)	Silquest A-1100 silane	Silquest VS-142 silane
Polyimide (PI)	Silquest A-1100 silane or Y-9669 silane	Silquest VS-142 silane

Thermosets

POLYMER MATRIX	SILANE TO CONSIDER	SILANE TO CONSIDER FOR LOW VOC
Epoxy (EP)	Silquest A-186 or A-187 silane	
Unsaturated Polyester (UP)	Silquest A-174NT silane	Silquest G-170 silane

General Considerations For Use

Fillers are typically treated by dissolving 2-5 wt% silane in an alcohol/water (90/10 by volume) mixture. Acidify non-amino silanes to pH =4 with acetic acid. The silane solution is applied to the filler using conventional equipment such as blender or mixers. If low VOC application is desired, silanes can be dissolved in a water only solution or applied as received to the filler with adequate mixing.

Patent Status: Nothing contained herein shall be construed to imply the nonexistence of any relevant patents or to constitute the permission, inducement or recommendation to practice any invention covered by any patent, without authority from the owner of the patent.

Product Safety, Handling and Storage: Customers should review the latest Safety Data Sheet (SDS) and label for product safety information, safe handling instructions, personal protective equipment if necessary, emergency service contact information, and any special storage conditions required for safety. Momentive Performance Materials (MPM) maintains an around-the-clock emergency service for its products. SDS are available at www.momentive.com or, upon request, from any MPM representative. For product storage and handling procedures to maintain the product quality within our stated specifications, please review Certificates of Analysis, which are available in the Order Center. Use of other materials in conjunction with MPM products (for example, primers) may require additional precautions. Please review and follow the safety information provided by the manufacturer of such other materials.

Limitations: Customers must evaluate Momentive Performance Materials products and make their own determination as to fitness of use in their particular applications.

THE MATERIALS, PRODUCTS AND SERVICES OF MOMENTIVE PERFORMANCE MATERIALS INC. AND ITS SUBSIDIARIES AND AFFILIATES (COLLECTIVELY "SUPPLIER"), ARE SOLD SUBJECT TO SUPPLIER'S STANDARD CONDITIONS OF SALE, WHICH ARE INCLUDED IN THE APPLICABLE DISTRIBUTOR OR OTHER SALES AGREEMENT, PRINTED ON THE BACK OF ORDER ACKNOWLEDGMENTS AND INVOICES, AND AVAILABLE UPON REQUEST. ALTHOUGH ANY INFORMATION, RECOMMENDATIONS, OR ADVICE CONTAINED HEREIN IS GIVEN IN GOOD FAITH, SUPPLIER MAKES NO WARRANTY OR GUARANTEE, EXPRESS OR IMPLIED, (i) THAT THE RESULTS DESCRIBED HEREIN WILL BE OBTAINED UNDER END-USE CONDITIONS, OR (ii) AS TO THE EFFECTIVENESS OR SAFETY OF ANY DESIGN INCORPORATING ITS PRODUCTS, MATERIALS, SERVICES, RECOMMENDATIONS OR ADVICE. EXCEPT AS PROVIDED IN SUPPLIER'S STANDARD CONDITIONS OF SALE, SUPPLIER AND ITS REPRESENTATIVES SHALL IN NO EVENT BE RESPONSIBLE FOR ANY LOSS RESULTING FROM ANY USE OF ITS MATERIALS, PRODUCTS OR SERVICES DESCRIBED HEREIN. Each user bears full responsibility for making its own determination as to the suitability of Supplier's materials, services, recommendations, or advice for its own particular use. Each user must identify and perform all tests and analyses necessary to assure that its finished parts incorporating Supplier's products, materials, or services will be safe and suitable for use under end use conditions. Nothing in this or any other document, nor any oral recommendation or advice, shall be deemed to alter, vary, supersede, or waive any provision of Supplier's standard Conditions of Sale or this Disclaimer, unless any such modification is specifically agreed to in a writing signed by Supplier. No statement contained herein concerning a possible or suggested use of any material, product, service or design is intended, or should be construed, to grant any license under any patent or other intellectual property right of Supplier covering such use or design, or as a recommendation for the use of such material, product, service or design in the infringement of any patent or other intellectual property right.

Momentive and the Momentive logo are trademarks of Momentive Performance Materials Inc.

*Silquest, Silquest A-187 and Silquest A-1100 are trademarks of Momentive Performance Materials Inc.