

## SilForce\* SL6210

### Description

SilForce SL6210 release coating is a Pt-concentrate that can be used with our thermal solventless system like SilForce SL6161, SilForce SL6961, etc., as a Pt source. SilForce SL6210 release coating can also be used in combination with SilForce SL6600E or other solventless pre-blend to increase the Pt-level. The SilForce SL6161 release coating system can improve the productivity, mainly on glassine and PE coated papers.

### Key Performance Properties

- Versatile system for all release liner (paper & films)
- New technology suitable for lower temperature curing
- New generation of inhibitor for fast system
- High flexibility in terms of formulations hold on phone
- Enhanced cross-linker for good anchorage of the release coating
- Productivity gain in terms of machine capacity

### Applications

SilForce SL6210 release coating used in combination with SilForce SL6161 or SilForce SL6600E (for example) and a cross-linker can be applied by any of the methods now being used commercially for solventless (and solvent based) silicone release coating. These include three rolls differential offset gravure and various multiple smooth rolls configurations. Heat should be applied immediately after coating to initiate cure. Best results are obtained with zoned ovens. Operating the first oven zone at 90~120°C will allow the coating to level, forming a continuous film before cure is initiated. Subsequent oven zones should be sufficiently high to achieve the required web exit temperature. Actual temperatures required for complete cure will be highly dependent on the performance of the oven and machine conditions. In general, minimum web temperature must be maintained a finite time(=dwell time) to obtain complete cure, the time dependent on oven length and the line speed.

### Instruction for Use

**Table 1 Typical starting formulations for glassine papers at a catalyst level of 50ppm**

Components	0% CRA	5% CRA	10% CRA
SilForce SL6161	95	90	85
SilForce SL6031		5	10
SilForce SL4330	3.3	3.6	3.9
SilForce SL6210	5	5	5

**Table 2 Typical starting formulations for PET films at a catalyst level of 100ppm**

Components	0% CRA	5% CRA	10% CRA
SilForce SL6600E	97.8	92.8	87.8
SilForce SL6630		5	10
SilForce SS4300(C/E)	2.9	3.1	3.3
SilForce SL6210	2.2	2.2	2.2
Anchorsil 2000	3	3	3

**Important Note:**

The suggested starting formulations in Table 1 and 2 are based on cure optimization. Destabilized(high) release may occur with some adhesive, solution acrylic in particular, at the suggested crossliner levels. Pls contact a Momentive Technical Service Representative for further information and guidance.

**Bath Life:**

The working life of an activated bath will vary depending on catalyst and inhibitors levels as well as ambient conditions. In general the suggested formulatioin in Table 1 and 2 will have a minimum bath life of 8 hours. The thin film bath life of the SilForce SL6161 system is significantly shorter than the thin film bath life of the SilForce SL6600E, SilForce SL6625, and SilForce SL6425 system.

**Bath Preparation**

- To ensure consistent results and maximize bath life, components should be mixed in the following order:
- 1: Weigh and add polymers (SilForce SL6161/SilForce SL6031 or SilForce SL6600E/ SilForce SL6630) to a clean, rust-free container/mixing vessel
  - 2: Weigh and add crossliner (SilForce SL4330) to above mix
  - 3: Agitate thoroughly
  - 4: Weigh and add the platinum concentrate (SilForce SL6210) to above mix
  - 5: Agitate thoroughly
  - 6: Weigh and add the Anchorsil2000 to above mix (when needed)
  - 7: Agitate thoroughly for 10-15mins to ensure homogeneity

Bath should be prepared just prior to use

**Coating Weight/Substrate**

SilForce SL6210 release coating used in combination with the SilForce SL6161 and SilForce SL6600E systems is suitable for a variety of papers. These include supercalendered kraft, glassine, clay coated kraft, etc. Coat weight will depend on the hold out and resolution of the surface. but generally 0.8~1.6g/m<sup>2</sup> will provide a contious silicone film.

Coat weights can be determined by x-Ray fluorescence. For machine trials, a simple, inexpensive method to calculate coat is available from Momentive.

**Specifications**

Typical product data values should not be used as specifications. Assistance and specifications are available at the technical service department of Momentive.

**FDA status**

SilForce SL6210 used in combination with the SilForce SL6161 and SilForce SL6600E system comply with FDA regulations 175.105, adhesive, 175.320, resinous and polymeric for polyolefin films 176.170, components of paper and paperboard in contact with aqueous and fatty foods, and 176.180, components of paper and paperboard in contact with dry foods.

**Containers**

18kg pail  
180kg drum

**Patent Status**

Nothing contained herein shall be construed to imply the nonexistence of any relevant patents or to constitute the permission, inducement or recommendation to practice any invention covered by any patent, without authority from the owner of the patent.

**Product Safety, Handling and Storage**

Correctly stored in its original, unopened container at 25°C or below SilForce SL6210 has a shelf life of 720\*\* days from the date of manufacturing. \*\*Please see also use-before/expiry date on product label and certificate.

SilForce SL4330 and other cross-linker used in combination with SilForce SL6210 will generate flammable hydrogen gas upon contact with strong acids, bases or oxidizing agents. Do not reuse the container. Customers should review the latest Safety Data Sheet (SDS) and label for product safety information, safe handling instructions, personal protective equipment if necessary, emergency service contact information, and any special storage conditions required for safety. Momentive Performance Materials (MPM) maintains an around-the-clock emergency service for its products. SDS are available at [www.momentive.com](http://www.momentive.com) or, upon request, from any MPM representative. For product storage and handling procedures to maintain the product quality within our stated specifications, please review Certificates of Analysis, which are available in the Order Center. Use of other materials in conjunction with MPM products (for example, primers) may require additional precautions. Please review and follow the safety information provided by the manufacturer of such other materials.

**Limitations**

Customers must evaluate Momentive Performance Materials products and make their own determination as to fitness of use in their particular applications.

**Contact Information**

For product prices, availability, or order placement, contact our customer service at [Momentive.com/CustomerService/](http://Momentive.com/CustomerService/)

For literature and technical assistance, visit our website at: [www.momentive.com](http://www.momentive.com)

**DISCLAIMER:**

**THE MATERIALS, PRODUCTS AND SERVICES OF MOMENTIVE PERFORMANCE MATERIALS INC. AND ITS SUBSIDIARIES AND AFFILIATES (COLLECTIVELY "SUPPLIER"), ARE SOLD SUBJECT TO SUPPLIER'S STANDARD CONDITIONS OF SALE, WHICH ARE INCLUDED IN THE APPLICABLE DISTRIBUTOR OR OTHER SALES AGREEMENT, PRINTED ON THE BACK OF ORDER ACKNOWLEDGMENTS AND INVOICES, AND AVAILABLE UPON REQUEST. ALTHOUGH ANY INFORMATION, RECOMMENDATIONS, OR ADVICE CONTAINED HEREIN IS GIVEN IN GOOD FAITH, SUPPLIER MAKES NO WARRANTY OR GUARANTEE, EXPRESS OR IMPLIED, (i) THAT THE RESULTS DESCRIBED HEREIN WILL BE OBTAINED UNDER END-USE CONDITIONS, OR (ii) AS TO THE EFFECTIVENESS OR SAFETY OF ANY DESIGN INCORPORATING ITS PRODUCTS, MATERIALS, SERVICES, RECOMMENDATIONS OR ADVICE. EXCEPT AS PROVIDED IN SUPPLIER'S STANDARD CONDITIONS OF SALE, SUPPLIER AND ITS REPRESENTATIVES SHALL IN NO EVENT BE RESPONSIBLE FOR ANY LOSS RESULTING FROM ANY USE OF ITS MATERIALS, PRODUCTS OR SERVICES DESCRIBED HEREIN.**

Each user bears full responsibility for making its own determination as to the suitability of Supplier's materials, services, recommendations, or advice for its own particular use. Each user must identify and perform all tests and analyses necessary to assure that its finished parts incorporating Supplier's products, materials, or services will be safe and suitable for use under end-use conditions. Nothing in this or any other document, nor any oral recommendation or advice, shall be deemed to alter, vary, supersede, or waive any provision of Supplier's standard Conditions of Sale or this Disclaimer, unless any such modification is specifically agreed to in a writing signed by Supplier. No statement contained herein concerning a possible or suggested use of any material, product, service or design is intended, or should be construed, to grant any license under any patent or other intellectual property right of Supplier covering such use or design, or as a recommendation for the use of such material, product, service or design in the infringement of any patent or other intellectual property right.

**Momentive and the Momentive logo are trademarks of Momentive Performance Materials Inc.**