

SilForce* SL6162 Release Coating

Product Description

This thermal solventless technology is most commonly used with glassine and PE coated kraft papers, where the cost saving will be most significant. Nevertheless, it can also be considered for use for kraft paper and PET films by adjusting the level of catalyst accordingly and selecting the right cross-linker. In combination with our new AnchorSil* 2000 and AnchorSil 3000 adhesion promoters, this thermal solventless system may be considered for use with untreated PET films. This system can improve the productivity.

Product References

SilForce SL6162 base polymer

SilForce SL6031 controlled release additive ⁽¹⁾

SilForce SL4320 cross-linker for papers ⁽²⁾

SilForce SL6210 concentrated catalyst (Pt)

⁽¹⁾ Other CRAs may be considered for this base polymer (please contact technical expert from Momentive for advice)

⁽²⁾ Depending on the substrate and/or the processing conditions other cross-linkers can be used

Key Features and Typical Benefits

- Versatile system for virtually all release liners (papers & films)
- New technology suitable for lower temperature curing
- New generation of inhibitor for fast system
- High flexibility in terms of formulations
- Concentrated catalyst outside of the pre-blends
- Enhanced cross-linker for good anchorage of the release coating
- Productivity gain in terms of machine capacity

Typical Physical Properties

Property	SilForce SL6162	SilForce SL6031
Viscosity, cstks, 25°C	170 - 300	1500 - 2700
Density, kg/l	0.97	1.05

Typical properties are average data and are not to be used as or develop specifications.

Containers

- 1 kg sample
- 18 kg pail
- 180 kg drum
- 950 kg tote

General Considerations for Use

This solventless release coating system can be applied by any of the methods now being used commercially for solventless silicone. These include three roll differential offset gravure and various multiple smooth roll configurations. Heat should be applied immediately after coating to initiate cure. Best results are obtained with zoned ovens. Operating the first oven zone at 90-120 °C will allow the coating to level, forming a continuous film before cure is initiated. Subsequent oven zones should be sufficiently high to achieve the required web exit temperature. Actual temperatures required for complete cure will be highly dependent on the performance of the oven and machine conditions. In general, minimum web temperature must be maintained a finite time (= dwell time) to obtain complete cure the time being dependent on oven length and the line speed.

Typical starting formulations for glassine papers at a catalyst level of 50 ppm

Component	0% CRA	5% CRA	10% CRA
SilForce SL6162 base polymer	95	90	85
SilForce SL6031 controlled release additive	-	5	10
SilForce SL4320 cross-linker for papers	3.2	3.5	3.8
SilForce SL6210 concentrated catalyst (Pt)	5	5	5

Typical starting formulation for PET films at a catalyst level of 50 ppm

Component	0% CRA	5% CRA	10% CRA
SilForce SL6162 base polymer	95	90	85
SilForce SL6031 controlled release additive	-	5	10
SilForce SL4320 cross-linker for papers	3.2	3.5	3.8
SilForce SL6210 concentrated catalyst (Pt)	5	5	5
AnchorSil* 2000	3	3	3

Important Note:

The suggested starting formulation in the table is based on cure optimization. Destabilized (high) release may occur with some adhesives, solution acrylics in particular, at the suggested cross-linker levels. Please contact a Momentive Performance Materials Technical Service Representative for further information and guidance.

Bath Life

The working life of an activated bath will vary depending on ambient conditions. In general, the suggested formulation in the table will have a minimum bath life of 4 hours. The thin film bath life of the SilForce SL6162 system is significantly shorter than the thin film bath life of the SilForce SL6600, SilForce SL6625 etc. systems. At high catalyst level (more than 80 ppm Platinum) bath life with SL6162 can be shorter.

Bath Preparation

To ensure consistent results and maximize bath life, components should be mixed in the following order:

1. Weigh and add SilForce SL6162 to a clean, rust-free container/mixing vessel
2. Weigh and add the cross-linker (SilForce SL4320) to the above material
3. Agitate thoroughly for 5 minutes to ensure homogeneity
4. Weigh and add the platinum concentrate (SilForce SL6210) to above mix
5. Agitate thoroughly for 10-15 minutes to ensure homogeneity.

Bath should be prepared just prior to use.

Coating Weight/Substrates

The optimal coat weight will depend on the hold out and resolution of the surface, but generally 0.8-1.6 g/m² will provide a continuous silicone film.

Coat weights can be determined by X-Ray Fluorescence.

Classification, Toxicity and Precautions

SilForce SL4320 cross-linker will generate flammable hydrogen gas upon contact with strong acids, bases or oxidizing agents. Do not reuse the container.

Intended Use

It is the obligation of the customer to examine Momentive's products as to their suitability for the intended use and application. Application, use and processing of the products by customer are beyond the control of Momentive and are therefore within the exclusive responsibility of customer.

Healthcare Applications

Momentive's products are industrial grade products and for industrial use only. They are not intended for use in certain medical applications involving long-term implantation into the human body (generally 30 days or more), direct ingestion, injection into the body or multiple-use contraceptive devices.

Patent Status

本書のいかなる内容も、関連特許が存在しないことを暗示したものではありません。またいかなる特許についても、その権利者による許可なしに、その特許が対象とする発明を実施するための許可、誘因または推奨を構成することはできません。

Product Safety, Handling and Storage

Customers should review the latest Safety Data Sheet (SDS) and label for product safety information, safe handling instructions, personal protective equipment if necessary, emergency service contact information, and any special storage conditions required for safety. Momentive Performance Materials (MPM) maintains an around-the-clock emergency service for its products. SDS are available at

www.momentive.com or, upon request, from any MPM representative. For product storage and handling procedures to maintain the product quality within our stated specifications, please review Certificates of Analysis, which are available in the Order Center. Use of other materials in conjunction with MPM products (for example, primers) may require additional precautions. Please review and follow the safety information provided by the manufacturer of such other materials.

Limitations

Customers must evaluate Momentive Performance Materials products and make their own determination as to fitness of use in their particular applications.

お問合せ窓口

製品の価格、取り扱い状況およびご注文については、Momentive.com/Contact us/ CustomerService/からカスタマーサービスへご連絡ください。

パンフレットおよび技術情報については、弊社ウェブサイトwww.momentive.comをご覧ください。

免責条項:

モメンティブ・パフォーマンス・マテリアルズならびにその子会社および関係会社(以下、総称して「サプライヤー」といいます)の素材、製品およびサービスは、サプライヤーの標準販売条件に基づき販売されています。この標準販売条件は、該当する販売代理店契約または販売契約に含まれており、注文確認書や請求書の裏面に印刷され、また要求に応じて提供可能です。本書に記載の情報、推奨、または提言は、誠意をもって提供されていますが、サプライヤーは明示的にも黙示的にも、(i)本書に記載の結果が最終使用条件下でも得られること、および(ii)製品、素材、サービス、推奨または提言に取り入れられている設計の有効性もしくは安全性について、いかなる保証もいたしません。サプライヤーの標準販売条件に定めのあるものを除き、サプライヤーおよびその代理人は、本書に記載の素材、製品またはサービスの使用によって生じたいかなる損害に対しても責任を負わないものとし、ます。サプライヤーの素材、サービス、推奨、または提言が、ユーザー自身の特定の使用目的に適しているか否かの判断については、各ユーザー自身が全面的に責任を負います。各ユーザーは、すべてのテストや分析を特定および実施して、サプライヤーの製品、素材、またはサービスが組み込まれている最終製品が安全であり、最終使用条件における使用に適していることを確認する必要があります。サプライヤーの署名入りの書面による合意がない限り、本書もしくはその他の文書または口頭による推奨または提言は、サプライヤーの標準販売条件の規定または本免責条項の変更、修正、優先、または権利放棄とはみなされないものとし、ます。本書に含まれる

素材、製品、サービスまたは設計の使用可能性または使用提案に関するいかなる記載も、当該使用または設計を対象とするサプライヤーの特許その他の知的財産権に基づくライセンスを付与することを意図してはならず、あるいはライセンスの付与と解釈してはならず、また、何らかの特許その他の知的財産権を侵害する素材、製品、サービスまたは設計の使用の提案を意図してはならず、また使用提案として解釈してはなりません。

Momentive および Momentiveのロゴは、Momentive Performance Materials Inc.の商標です。